

Eaton 10250T411LRD06-1

Catalog Number: 10250T411LRD06-1

Eaton 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Extended, Red actuator, LED, transformer light unit, 1NO-1NC, 120 Vac light unit, Chrome bezel, 6 Vac/dc lamp, Plastic actuator



General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T411LRD06-1
UPC	Product Length/Depth
782114710357	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

Product specifications

Application

Pushbutton

Special features

10250T series

Type

30.5 mm, Heavy-Duty

Actuator color

Red

Bezel

Chrome

Actuator material

Plastic

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Series

10250T

Lamp voltage - max

6 V

Lamp voltage - min

6 V

Light unit type

LED, transformer

Light unit voltage

120 Vac

Rating

NEMA 13

NEMA 12

NEMA 3

NEMA 4X

Resources

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T411LRD06-1](#)

NEMA 4
NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia