

# Eaton BR120

Catalog Number: BR120

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, single-pole, 120/240V, BR, #14-4 AWG Cu/Al, Q1, Type BR loadcenters

## General specifications



### Product Name

Eaton BR thermal magnetic circuit breaker

### Catalog Number

BR120

### UPC

786676362108

### Product Length/Depth

2.5 in

### Product Height

3 in

### Product Width

1 in

### Product Weight

0.3 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Compliances

Federal Specifications Classification W-C375

### Certifications

UL 489

## Product specifications

### Used with

Type BR Loadcenters

### Type

Type BR 1-Inch plug-on circuit breaker

### Amperage Rating

20 A

### Voltage rating

120/240 V

### Circuit breaker type

BR

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Single-pole

### Quantity

1

## Resources

### Brochures

### Specifications and datasheets

Eaton Specification Sheet - BR120

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia