

Eaton BR1515

Catalog Number: BR1515

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 15-15 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, BR, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR1515
	UPC
	786676370059
Product Length/Depth	Product Height
1 in	2.5 in
Product Width	Product Weight
2.9 in	0.35 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Product specifications

Used with

Type BR Loadcenters

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

(2) 15A

Voltage rating

120/240 V

Circuit breaker type

BR

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR1515](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia