

Eaton BR250

Catalog Number: BR250

Eaton BR Thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 50 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR250
	UPC
	786676363051
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
2 in	0.5 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Product specifications

Used with

Type BR Loadcenters

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - BR250](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)