

Eaton C440A1A045SAX

Catalog Number: C440A1A045SAX

Eaton C440 electronic overload relay, C440 Electronic Overload Relay - NEMA, Separate Mount, 45mm frame, Selectable 10A, Class 10 ,20, 30, Overload 9-45A, Standard

General specifications



Product Name

Eaton C440 electronic overload relay

Catalog Number

C440A1A045SAX

UPC

786685412375

Product Length/Depth

4.32 in

Product Height

3.8 in

Product Width

1.8 in

Product Weight

0.87 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

UL Listed
CSA Certified

Product specifications

Overload range

9-45A

Special features

Standard

Type

Electronic overload relay

Frame size

45 mm

Rated short-time withstand current (I_{cw})

Auto

Manual

Trip type

Selectable 10 A, class 10 ,20, 30

Size

Separate Mount

Resources

Brochures

[C440 Electronic Overload Relay](#)

Specifications and datasheets

[Eaton Specification Sheet - C440A1A045SAX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia