

Eaton CHF230

Catalog Number: CHF230

Eaton CH Thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF, Type CH Loadcenters



General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CHF230
	UPC
	786685361901
Product Length/Depth	Product Height
1.5 in	2.6 in
Product Width	Product Weight
0.75 in	0.28 lb
Warranty	Compliances
Limited lifetime residential, 1 year commercial	HACR Rated
	Certifications
	UL 489

Catalog Notes
HACR Rated. Two-Pole 120/240V
Common Trip Requires Two 3/4-Inch Spaces. With Trip Indication

Product specifications

Used with

Type CH Loadcenters

Type

Type CHF 3/4-Inch standard circuit breaker

Amperage Rating

30 A

Voltage rating

120/240 V

Trip Type

Trip flag

Circuit breaker type

CHF

Interrupt rating

10 kAIC

Main circuit breaker

CHF

Wire size

(1) #14-8 AWG

(2) #14-10 AWG Cu/Al

Number of poles

Two-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHF230](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia