

# Eaton E47BML04

Catalog Number: E47BML04

Eaton E47 Precision Limit Switch, Basic, Extended Straight Plunger, Mineral Filled Phenolic enclosure, 15A max AC, 15A max DC, SPDT, 15A at 125Vac / 15A at 14Vdc, Solder Terminals

## General specifications



Product Name

Eaton E47 limit switch

Catalog Number

E47BML04

UPC

782113770871

Product Length/Depth

0.69 in

Product Height

0.7 in

Product Width

1.36 in

Product Weight

0.1 lb

Warranty

1 year

Compliances

CE Marked

Certifications

CSA Certified

UL Listed

Catalog Notes

Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 - 12 AWG (2.5 sq. mm maximum)

## Product specifications

### Type

E47

### Contact Rating

15A at 125Vac / 15A at 14Vdc

### Enclosure material

Mineral filled phenolic

### Connection

Solder terminals

### Contact configuration

SPDT

### Switch type

Extended straight plunger

### Operating temperature - max

176 °F

### Operating temperature - min

-13 °F

### Environmental rating

NEMA 1

### Maximum AC current

15 A

### Maximum DC current

15 A

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - E47BML04](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)