

Eaton XTCE015B01A

Catalog Number: XTCE015B01A

Eaton XT IEC contactor, 15A, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NC, 15A, Frame B, 45 mm, 50-60 Hz, 1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

EAN

4015082900908

Product Height

1.5 in

Product Weight

0.5070632 lb

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Number

XTCE015B01A

Product Length/Depth

4 in

Product Width

3.5 in

Compliances

RoHS Compliant
CE Marked

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

15A

HP rating - max

1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NC

Continuous ampere rating

15 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCE015B01A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia