

Eaton XTCE025C10TD

Catalog Number: XTCE025C10TD

Eaton XT IEC contactor, 25A, 24-27 Vdc, 1NO, 25A, Frame C, 45 mm, 2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE025C10TD

EAN

4015082771461

Product Length/Depth

4 in

Product Height

2 in

Product Width

3.5 in

Product Weight

1.2 lb

Compliances

RoHS Compliant
CE Marked

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

25A

HP rating - max

2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

24-27 Vdc

Contact configuration

1 NO

Continuous ampere rating

25 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCE025C10TD](#)