

Eaton XTCE080F00B

Catalog Number: XTCE080F00B

Eaton XT IEC contactor, 80A, 220 Vac 50 Hz, 240 Vac 60 Hz, 0NO-0NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE080F00B

EAN

4015082394011

Product Length/Depth

6.2992126 in

Product Height

6.69291339 in

Product Width

4.37007874 in

Product Weight

0.5070632 lb

Certifications

UL Listed

CSA Certified

Product specifications

Amperage Rating

80A

HP rating - max

7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

220-240 Vac, 50/60 Hz

Contact configuration

0 NO, 0 NC

Continuous ampere rating

80 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCE080F00B](#)