

PA-UL-LNB46.R001



*picture only for reference

Dimensions

Length	67	± 1mm
Width	18.6	± 0.5mm
Height	41	± 1mm



MH45979



IEC 62133 2nd. Ed.

Data for Pack

Nominal voltage	3.6V	2.5V - 4.2V
Nominal capacity	6700mAh	typical
Used cell in pack	2pcs	Panasonic NCR-18650BF
Internal resistance pack	100mΩ	±10%
Charge voltage	4.2V	max
Charge current	standard	1.1A
	rapid	2.4A
Discharge	standard	1.1A
	max cont.	3A
	max peak	10A
Short circuit current	≤ 63A	< 380μs
NTC	10kΩ	Tolerance ±3%; B-value 25°C/85°C = 3980K
Connector	JST	XHP-3
		Pin1 GND
		Pin2 NTC
Cable Length	45mm	± 5mm
		± 5g
Weight	ca. 90g	± 5g
Watt-hour rating	24Wh	acc. to UN38.3 Certificate

*1) discharge in ambient temperatures lower than 0°C will result in limited performance in current output and usable capacity

Limitations by Safety Unit (SU) @ Ta 25°C

over voltage (per cell)	cut off	4215mV	±25mV
	release	4100mV	±25mV
under voltage (per cell)	cut off	2300mV	±50mV
	release	2400mV	±50mV
Current Limit 1 by SU		≤ 4A	continous typical
Current Limit 2 by SU		≥17.9A	2.24ms (typical)
short circuit protection		≥42.9A	380μs (typical) ±10A
Power consumption	active	15μA	±5μA
	power down	8μA	±2μA

Recommended Charger

C-LIO-1SN15-1,8M-DIN4-GPN-.R001