

# Coaxial Cable RG62A/U

**multicomp**PRO

**RoHS  
Compliant**




## Specification

No.	Item	Structure	Material	Colour
1	Inner conductor	1/0.643 +0.01mm	CCS	Yellow
2	Wrap	2.45 +0.2mm	PE	White
3	Insulation	3.7 +0.2mm	PE	White
4	Wire braid	112mm × 0.16mm	Bare copper	Yellow
5	Jacket	6.15+0.2mm	PVC	Black

## Electrical physical and properties of product

Item	Unit	Value
Capacitance	pF/m	47+5
Impedance	Ω	93±5
Bent radius	mm	62
Max voltage	VMS	1500
Max Frequency	MHz	1000
Temperature scope	°C	-20 to +80
Attenuation constant at 20°C (Permissible error 15%)	400MHz	26.3
	1000MHz	42.7

## Diagram



## Part Number Table

Description	Part Number
Coaxial Cable, RG62A/U, 93 Ohm, PE, PVC, Black, 100m	MP014016

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO