



Sample photo

Order symbol: MCE FEM 14 MF/M
Product nbr: 7221181

Description: DIN rail modular enclosure
Remarks:

EAN: 6418074007681
EI. number:
 Finland 3424414
 Denmark 8212029127
 Italy 7750140

Including: Modular component enclosure with TPE gaskets, mounted DIN 35-rail, wall mount cover plugs and mounting instructions. PC/FEM only: two PEN 10 mm² bars mounted, Multi-FEM and FEM membrane cable glands, module marking stripe and pocket.

Dimensions:	L	W	H
mm:	280	306	145
inch:	11	12	5.7

Materials:

Material:	PS
Base colour:	RAL 7035
Cover colour:	Smoked grey
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	TPE

Temperatures:

Short term:	-30 ... 80 °C
Continuous:	-30 ... 60 °C
Short term:	-22 ... 175 °F
Continuous:	-22 ... 140 °F

Accessories:

PEN 16x10	PEN-bar for MCE 14
PEN 35x10	PEN-bar for MCE 28+
PEN H 26140	PEN-bar holder for MCE 14+
MCE 14 PEN SET	Mounting ready PE/N/PEN -rail set
MCE MU PEN SET	Multiadapter set
FP 26128	Fastening lug set
FP 26127	Fastening lug set
FP A 26133	Front plate
MR 26065	Key lock set

Rating:

Ingress Protection (EN 60529):	IP 55
Impact Resistance (EN 50102):	IK 07
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
Flammability Rating (UL 746 C 5):	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	750

Certificates:

