

Technical data sheet

Article number:
111-91000

MLT8SSC5

Product Group	Cable Ties with Fold Locking and Coating
Product Family	MLT-C
Material	Stainless Steel (SS316L), Polyester (SP)
Colour	Black (BK)
Application Tool	HDT16
Bundle Diameter max (metric)	60 mm
Bundle Ø min.	20.0 mm
Flammability	non-burning (except coating)
Halogen-free	Yes
Length (L)	230 mm
Min.Tensile Strength	420 N
Operating Temperature	-80 °C to +538 °C
Package Content packed in	bag
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	Yes
Thickness (T)	0.7 mm
Variant	Not Serrated
Weight/Unit	0.005 kg
Width (W)	5.26 mm

HF ✓

LFH ✓

RoHS ✓