

EKP30-T2FSH280



Sample image

Order symbol : EKP30-T2FSH280

Product nr : 3620143

Description : Hinged cover, PC

Remarks : Transparent, hinges on short side

EAN : 6418074029775

El. number :

- Finland : 3424824
- Denmark : 8212012697
- Sweden : 2507791

Dimensions :	Height	Width	Depth
mm :	380	280	30
inch :	14.96	11.02	1.18

Materials :

Material :	Polycarbonate
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Not insulated
UV resistance :	-
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175