



Pushing Performance
Since 1945

Han Q7/0_I_F_PIT_0.14-1.5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 007 5101
Specification	Han Q7/0_I_F_PIT_0.14-1.5mm²
HARTING eCatalogue	https://b2b.harting.com/09120075101

Identification

Category	Inserts
Series	Han® Q
Identification	7/0

Version

Termination method	Push-In
Gender	Female
Size	3 A
Number of contacts	7
PE contact	Yes

Technical characteristics

Conductor cross-section	0.14 ... 1.5 mm²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	19.9 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140447912
eCl@ss	27440205 Contact insert for industrial connectors