



Pushing Performance  
Since 1945

# Han Q8/0\_I\_M\_PIT\_0.5-2.5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 5001
Specification	Han Q8/0_I_M_PIT_0.5-2.5mm²
HARTING eCatalogue	<a href="https://b2b.harting.com/09120085001">https://b2b.harting.com/09120085001</a>

## Identification

Category	Inserts
Series	Han® Q
Identification	8/0

## Version

Termination method	Push-In
Gender	Male
Size	Han-Compact®
Number of contacts	8
PE contact	Yes

## Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm²
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



**Pushing Performance**  
Since 1945

## Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	10
Net weight	34.68 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140935020
eCl@ss	27440205 Contact insert for industrial connectors