

RoHS  
Compliant



## Specification

Product Size : 380mm x 295mm x 82mm  
Product Weight : 4300g (With Blow Mold Case)  
Main Material : Chrome Vanadium and Carbon Steel

## Content

- 6 Pcs Screwdriver 6 x 100- / 6 x 100+ / 5 x 75- / 5 x 75+ / 6 x 38- / 6 x 38 + 1PC Bit Handle
- 5 Pcs Precision Screwdriver 3.0- / 2.4- / 1.8- / 3.0+ / 2.4 + 1PC Ratchet Handle 1PC AD
- 1 PC Water Pump Plier 10"
- 12 Pcs 1/4 Dr Socket 4-4.5-5-5.5-6-7-8-9-10-11-12-13mm
- 1 Pc 1/4 Dr. Extension Bar 2"
- 9 Pcs Hex Key
- 1 Pc 9" Level
- 1 Pc Measure Tape 5M
- 1 Pc 300g Hammer
- 1 Pc Combination Pliers 8"
- 1 Pc Long Nose Pliers 8"
- 40 Pcs Bits
- 100 Pcs Assorted Fasteners
- 1 Pc Blow Case

Warranty: 03 years

## Part Number Table

Description	Part Number
Tool Set, 183 Pcs	MP013668

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.