

Ferrule Kit Uninsulated, 5 Types






EN0506








http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

Ferrule Kit Uninsulated, 5 Types





Surface treatment : Tin plated.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk



Ferrule Kit Uninsulated, 5 Types



Specification Table

ltem	Maximum Electric Current		
	AWG	AMP	Wire Range
EN0506	22	9	22 AWG (0.50 mm ²)
EN1010	18	17	18 AWG (1.0 mm ²)
EN1510	16	18	16 AWG (1.5 mm ²)
EN2512	14	30	14 AWG (2.5 mm ²)
EN7510	20	12	20 AWG (0.75 mm ²)

Part Number Table

Description	Part Number
Ferrule Kit, Uninsulated, 5 Types	XRBOX5-EN-EA481

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheets previously for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2009.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

