

K30LBXXPQP

► K30 CORE SERIES 30 MM GENERAL PURPOSE LED INDICATOR



K30 Series EZ-LIGHT: 1-Color General Purpose Indicator

Voltage: 10-30 V dc; Housing: Polycarbonate; IP67

Input: PNP; Color: Blue

150 mm (6 in) 4-pin M12 PVC Pigtail QD

Part Number: 83493

CERTIFICATIONS



SPECIFICATIONS

IP Rating	IP67, IP69K
Display	No
NEMA / UL Type Rating	UL 4X, 13
Power	DC
Cable Length (m)	0.15
Housing Style	Base Mount - Dome Window
Primary Housing Material	Polycarbonate
Indication	Yes
Mounting Thread	M22 x 1.5
Color Input Control	Individual (One wire/color, same number of colors as input wires)

Number of Colors	1
Product Size (mm)	30
Color Technology	Standard LED
Color Option 1	Blue
Animation Option 1	Solid On
Connection	Pigtail QD
Quick Disconnect Type	M12
Max Current Color (mA)	25
Number of Input Pins/Conductors	4
Supply Voltage	10-30 V dc
Input Type	PNP
Max Input Response Time (ms)	1
Physical Dimensions (LxWxH or DxH mm)	30.0 x 44.5
Environmental Rating	IP67; IP69K
Max Op. Relative Humidity Non-Condensing (%)	90% @ 50°C
High Temperature (up to 100° C)	50
Min Op. Temperature (°C)	-40
Storage Temp (°C)	-40 to 70
Primary Housing Color	Black
Primary Window Material	Polycarbonate Diffused
Feature: Washdown Rated	Yes
Feature: Audible	No
Multi-Color Device	Single Color On
Feature: Quick Disconnect	Yes

EPLAN Status	Published
EPLAN Original Sent Date	05/29/2024