

Anybus CompactCom 40 Starter Kit - Pluggable Brick

Item number: 023220-B

The Anybus CompactCom Starter Kit enables evaluation and demonstration of different applications and use cases in a Windows environment. It offers instant access to CompactCom when combined with Anybus' Host Application Example Code. Please note, Anybus CompactCom Bricks and connector boards must be ordered separately.



Evaluate the CompactCom Pluggable Brick and its API before starting your integration

Features and benefits

- ✓ **Comprehensive evaluation**
Enables thorough evaluation of Anybus CompactCom capabilities and all of its host communication interfaces.
- ✓ **Evaluate from a Windows PC**
Connects to a Windows PC via the included USB cable and Anybus' Transport Provider software.
- ✓ **Network flexibility**
Facilitates trying out different network combinations.
- ✓ **All-inclusive package**
Includes essential boards, adapters, and cables for evaluation. CompactCom Bricks and connector boards are sold separately.
- ✓ **Get started quickly!**
The Host Application Example Code includes a Visual Studio project ported for Windows.

Anybus CompactCom 40 Starter Kit - Pluggable Brick



General

Net Weight (g)	1510
Packed Width (mm)	35
Packed Height (mm)	8
Packed Depth (mm)	28
Packed Weight (g)	1510
Operating Temperature °C Min	0
Operating Temperature °C Max	70
Storage Temperature °C Min	-40
Storage Temperature °C Max	85
Input Voltage (V)	24 VDC, +/- 20%
Not Included (in delivery)	CompactCom Bricks(s) and connector board(s)
Warranty (years)	1 year

Identification and Status

Product ID	023220-B
Country of Origin	Sweden
HS Code	8517620000
Export Control Classification Number (ECCN)	EAR99
Supply Risk Factor ERP	Used in Volume 01