

Eaton HEX-KW-DRYC

Catalog Number: HEX-KW-DRYC

Eaton Bussmann series HET inline fuse holder, 0-30 A, Two-pole, Loadside: Copper setscrew (2) #12-3, Lineside: Copper setscrew (2) #12-3, 600 V, Used with Class CC and 13/32" x 1 1/2" fuses

General specifications



Product Name	Catalog Number
Eaton Bussmann series HEX inline fuse holder	HEX-KW-DRYC
	UPC
	051712539913
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.85 lb
Warranty	Compliances
Not Applicable	RoHS Compliant
Certifications	
Contact Manufacturer	
UL Recognized	
CSA Certified	

Electrical rating

Amperage Rating

0-30A

Voltage rating

600 V

Physical details

Number of Poles

Two-pole

General information

Connection

Lineside: Copper setscrew (2) #12-3

Loadside: Copper setscrew (2) #12-3

Used with

Used with Class CC and 13/32" x 1 1/2" fuses

Resources

Catalogs

[HEX-KW-DRYC~BUSS FUSEHOLDER](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - HEX-KW-DRYC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia