






Technical specification:

Technische Daten:

Rated Voltage/ Bemessungsspannung: IEC 61076-2-101	50 V AC / 60 V DC
Current rating/ Strombelastbarkeit: IEC 61076-2-101	3 A at / bei 40°C
Insulation resistance/ Isolationswiderstand: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree/ Verschmutzungsgrad: IEC 60664-1	3/2
Degree of protection/ Schutzart: IEC 60529	IP 67, in mated condition/ im verschraubten Zustand
Temperature range/ Umgebungstemperatur: EN 60512-11-10 EN 60512-11-4	-25°C ... +80°C -40°C -40°C ... +85°C
Mating cycles/ Steckzyklen: IEC 60512-9a	≥ 100

Cable specification:

Kabeleigenschaften:

Temperatur range/ Umgebungstemperatur: static/fest verlegt flexible/bewegt	-25°C ... +80°C -5°C ... +80°C
---	-----------------------------------

Materials/

Werkstoffe:

Contact/ Kontakt:	CuZn, Ni b / Au 0,2 gal.
Contact carrier/ Kontaktträger:	PA, UL 94 V-0
Moulding body/ Griffkörper:	TPU, UL 94 HB, grey / grau

Contact assignment/


Kontaktbelegung:

- 1) brown / braun
- 2) white / weiß
- 3) blue / blau
- 4) black / schwarz

Conec part no/ Conec Art.-nr.:	Description/ Bezeichnung:	Length L/ Länge L:	Cable/ Kabel:
42 - 13083	SAL - 8 - RKS4 - RSS4 - 0,3 / A1 / 034	0,3m	PVC, grey / grau, 4x0,34mm ² , 4LiYY Cable / Kabel: 781-A13400
42 - 13084	SAL - 8 - RKS4 - RSS4 - 0,6 / A1 / 034	0,6m	
42 - 13085	SAL - 8 - RKS4 - RSS4 - 1,5 / A1 / 034	1,5m	
42 - 13086	SAL - 8 - RKS4 - RSS4 - 3 / A1 / 034	3m	
42 - xxxxx	SAL - 8 - RKS4 - RSS4 - ... / A1 / 034	x	

tolerance of cable/
Kabeltoleranz:

L ≤ 4m: L + 40mm
L > 4m: L + 1%



dim. in mm

general tolerance/
Allgemeintoleranz:

0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm
* ± 5°

	Date/Datum	Name
drawn/ gez.	21.08.2018	Becker
appd./ gepr.	21.08.2018	Wietfeld

Connecting cable Ø8,
female connector axial - male connector axial, snap
Verbindungsleitung Ø8,
Kupplung axial - Stecker axial, snap

Index: a Original

Status: Freigegeben

RoHS & REACH compliant/konform

scale/Maßstab:
1,5:1
(2:1)

CONEC®

dwg no /
Z.-nr.:

42K1A1795

DIN-
A4

1 / 1