







used for: DUAL-PORT

Directive 2002/95/EC
RoHS
Compliant

SPECIFICATION:

- MATERIAL:**
INSULATOR: THERMAL PLASTIC UL 94 V-0, COLOR: BLACK
CONTACTS: BRASS
SHELL: STEEL
RIVET, BOARDLOCK: COPPER ALLOY
- CONTACT PLATING:**
UNDERPLATE: 50µin NICKEL
CONTACT AREA: GOLD FLASH
SOLDER TAILS AREA: 100µin TIN
- ELECTRICAL:**
CURRENT RATING: 3 Amps max.
CONTACT RESISTANCE: 25 mOhm max.
INSULATION RESISTANCE: 3000 MOhm min. @ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC / MINUTE
OPERATING TEMPERATURE: -55°C TO +105°C
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: ±0.10mm

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	ANG.	±5°
	0	±0.5
	a	±0.3
	Ø	±0.2
dim. in mm		
2008	date	name
drawn	21.01.	Lehmenkühler
appd.	21.01.	Kühle
norm		
d-old		

scale:	2:1
material:	SEE NOTES
title:	
DUAL-PORT 15.88mm	
D-SUB MALE 25pos. / D-SUB FEMALE 25pos. with PCB clip	
dwg no:	AutoCAD 2006
16K1A2230	
part no:	DLS3PS5AN21X
DIN-A	3
sh:	1/1