






STRIPPING DIMENSIONS



Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance			dim. in mm
drawn	19.07.10 Schmidt		
appd.	19.07.10 Fischer		
norm			
d-old			
CONEC®			

scale:	10:1		
material:			
title:	COAXIAL CONTACT PLUG 50 OHM inner conductor for solder termination outer conductor for crimp or solder termination		
dwg no:	Inventor 10	DIN-A3	
	13K1A3339	sh: 1	
part no:	131A20049X		