







STRIPPING DIMENSIONS (5 : 1)



APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND			
rev.	description	date	name
a	Origin		

tolerance	
dim. in mm	
date	name
drawn	10.01.08 Lehmenkühler
appd.	10.01.08 Mickenbecker
norm	
d-old	

scale:	10:1 (5:1)	
material:		
title:	COAXIAL CONTACT MALE 90° 50 OHM, Inner conductor for solder termination outer conductor for crimp or solder termination	
dwg no:	Inventor 10	DIN-A3
	13K2A067A	sh: 1
part no:	131J22029X	

Directive 2002/95/EC
„RoHS“
Compliant

