






Directive 2002/95/EC RoHS compliant

Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos. 4/5
132J35019X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
132A35019X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance		 dim. in mm	scale: 5:1		
								material: see table		
						date	name		title: COAXIAL CONTACT SOCKET 75 OHM Solder termination 90° with 3 pins for D-SUB COMBINATION	
						drawn 28.07.99	Barcinski			
						appd. 28.07.99	Mickenbecker			
						norm				
						d-old			dwg no: 13K2IR4A	
	2 x b	Ä4600	11.01.2013	K.H.			DIN-A3			
	a	Original								
	rev.	description	date	name			part no:  see table			