





VIEWS WITHOUT TETHER




NOTES:

1. MATERIAL AND FINISH:

- COUPLER RING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
- COVER HOUSING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
- TETHER: PE-SW (BLACK),
- INTERFACIAL SEAL: SILICONE; COLOR: WHITE
- RETAINING RING: STAINLESS STEEL

2. OPERATING TEMPERATURE: -40 °C to +85 °C

3. IP67 RATED WHEN COVERED OR FULLY MATED WITH THE APPROPRIATE MATING CONNECTOR



RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (1:1)				
							material: see notes				
								date	name	title: Protective Cover Ⓟ for IP67 Duplex Power 3pos Female Receptacle Assembly	
								drawn 20.04.15	Henneboel		
								appd. 20.04.15	Koch		
				norm							
				d-old		dwg no:		DIN-A3			
1 x b	Ä6182	06.06.2016	K.H.								
a	Original					sh: 1					
rev.	description	date	name			part no:		17-400400			

Protective Cover
for IP67 Duplex Power 3pos
Female Receptacle Assembly

17K1A463

DIN-A3
sh: 1