






Materials:

Socket housing: CuZn
Housing surface: nickel plated
Sealing: FPM, NBR


Installation specification:

Recommended torque: 1-1,2 Nm
Conec installation tool: Torque wrench: 36-000200
Insert across flats 13: 36-000220
Installation hole: See fig.1 42K1A1119

DO NOT ALTER CAD DRAWING BY HAND

RoHS & REACH compliant

Index: a 25.04.16 rbo Ä6018
Installation specification added



dim. in mm

	date	name
drawn	17.08.15	Gitinow
appd.	17.08.15	Schramm

general tolerance: 0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm
+ ± 5°

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

CONEC®

title:

Housing female M10x1 H13,
frontmounting

dwg no:

42K1A1079

part no:

42-01482