





2 CONTACTS WILL BE SUPPLIED LOOSE

STRIPPING DIMENSIONS



NOTES:

- MATERIAL AND FINISH:**
 - COUPLER RING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
 - HOUSING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
 - CABLE GLAND: PA (BLACK), UL94 V-0; UL (f1) RATED
 - CABLE GLAND RUBBER RING: NBR; COLOR: BLACK
 - CABLE FITTING: PA (BLACK); UL94 V-0; UL (f1) RATED
 - INTERFACIAL SEAL: SILICONE; COLOR: RED
 - RETAINING RING: STAINLESS STEEL
- HIGH POWER CONTACTS; CRIMP; 30A**
 - FOR USE WITH CABLE AWG 8* - 10
 - MATERIAL: COPPER ALLOY
 - PLATING, MATING AREA: GOLD FLASH over NICKEL
 - PLATING, TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
 - CONTACTS WILL BE SUPPLIED LOOSE
 - CRIMPING: USE CRIMP TOOL 360X10409X WITH TOOL INSERT 360X20029X
 - SELECTOR SETTINGS: 5 FOR AWG 8*; 4 FOR AWG 10
- OPERATING TEMPERATURE: -40°C to +100°C**
- WORKING VOLTAGE: 48V AC/DC**
- IP67 RATED WHEN COVERED OR FULLY MATED WITH THE APPROPRIATE MATING CONNECTOR**
- *NOTE: FOR AWG 8 STRANDED 19/21, 37/24 and 65/26 WIRE ONLY**

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						scale:	1,5:1
						material:	SEE NOTES
						title:	IP67 POWER BAYONET 2pos SOCKET KIT / CRIMP cable mount Ø6-12mm
						dwg no:	17K1A480
DO NOT ALTER CAD DRAWING BY HAND						DIN-A3 sh: 1	
rev.	a	Original	description	date	name	part no:	17-400523

RoHS compliant