


All rights reserved. No copies
Unless written permission from Rose.
Drawing may not be passed to
third parties or misused in any way.

Montage für Klarsichthaube
Mounting for transparent cover



Alternative :
up to 7mm wall thickness Pos.35 (M4x14),
from 7mm wall thickness Pos.30 (M4x16).

© Montage mit Feder nur bei Polyestergehäusen !
 Mounting with spring only for polyester enclosures !

Pos.65

Pos.60

Pos.65

Spannhülse clamp sleeve

Be
 be
 Ma
 da

Bearbeitung und Montage bei beschädigter Schraubensicherung.
Machining and mounting in case of damaged screw locking.

machining:	
transparent cover	according to drawing no. 13-2-343100-01-1
front frame	according to drawing no. 13-2-080600-02-1
hinge-base	according to drawing no. 10-2-126500-02-0

Gehäuse- und Deckelbearbeitung nach Zeichnung-Nr.: 10-2-010560-02-1
enclosures- and lid manufacturing according to drawing no. 10-2-010560-02-1

d	Korrektur / Correction	5364	06.05.10	T.		
c	Übers./Po.20 geß./Po.50+60hinzu	5211	19.08.08	AM		
b	Pos.35 hinzu, Bearb. ergänzt	4063	08.06.00	T.	Farbe/colour	
a	Unterlegsch. Pos.65 hinzu	3465	24.09.99	T.	Gewicht/weight	
Index	Änderung/Modifikation	Änd.-Nr. Mod.-No.	Datum / Date / Name		Werkstoff/Material	
	Systemtechnik GmbH	Bearb. issued	09.10.95	T.	Oberfläche/Surface	
	32457 Porta Westfalica	geprüft checked	06.05.10	Slg.	Freimaßtoleranz Open Tolerances	
Maßstab Scale	Benennung/Description				Werkstückkanten/Edges	
1:1	Außengelenk—Montage				Ersatz für Replacement for	
	External hinges—mounting				Zeichnung—Nr.:/Drawing—No.:	
					10—4—027001—01—0	