

Product Specification PDF

Date	Correct as of 27th Sep 2019
Brand	C.K
Product	T37021 180
Description	RedLine VDE High Leverage Side Cutters 180mm
Barcode	5051074310231
Commodity code	8203200000
Country of origin	DE



Features & Benefits	~ VDE approved ~ individually tested to 10,000V for safe live working up to 1,000V ~ New, 33 % slimmer design for greater accessibility in tight access areas ~ New optimised cutting jaw geometry for improved cutting performance ~ Induction hardened jaws for outstanding long term performance ~ Special alloy steel, drop forged, hardened and tempered for exceptional strength and durability ~ Two component, ergonomic design, with anti-slip horns for increased comfort, control and safety ~ Length: 180 mm ~ Cutting capacities: hard: 2,2 mm / medium hard: 3,8 mm / soft: > 6,0 mm
Applicable Standards	EN 60900 , VDE 682/2 1, ASTM-F 1505
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	3	60
Width mm	62	62	88	395
Depth mm	25	25	252	600
Height mm	180	252	62	210
Weight	215	229	747	15.8
Packaging Information	Card use	0	Box	Case
	Card gms	0	60	900
	Plastic use	Hanger	0	-
	Plastic gms	14	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0