

Product Specification PDF

Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3892
Description	Ecotronic ESD Long Snipe Nose Pliers (Bent)
Barcode	5013969938920
Commodity code	8203200000
Country of origin	TW



Features & Benefits	Lightweight, precision snipe-nose pliers with 45° bent tips Long, serrated jaws Rounded outer edges for reduced risk of damage to surrounding components For the safe handling of small components in fine applications (e.g microelectronics and precision mechanics) Special tool steel body, hardened for long-term performance Black oxidised finish for corrosion resistance and reduced glare Electro-static discharging handles ~ dissipative 10 ⁷ Contoured, dual component handle design for comfortable working Smooth-action return spring for convenience during repetitive work Joint with durable stainless steel rivet Technical information: Total length: 152 mm Head Height (from joint to tip): 39 mm Head Width (Widest point): 12 mm Height at tips: 1 mm Steel Thickness: 3 mm
Applicable Standards	IEC 61340 5.1 & 5.2
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	120
Width mm	152	220	21.6	470
Depth mm	70	80	8.4	470
Height mm	20	2.5	10.8	240
Weight	85	100	669	14.4
Packaging Information	Card use	0	Box	Case
	Card gms	0	69	1012.5
	Plastic use	Blister	0	-
	Plastic gms	15	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0