Product Specification PDF



Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3012
Description	High Speed Steel Multi-Step Drill 12.5 - 32.5mm
Barcode	5013969978056
Commodity code	8207506000
Country of origin	DE



Features & Benefits

 \sim Centres, drills and deburs sheet metals in one operation \sim HSS, precision ground for accurate drilling \sim Dual flute construction for faster drilling & longer life \sim Three flats on drive shaft for secure drive in drill chucks \sim Cuts hole sizes: 12,5 / 12,7 / 15,2 / 16,2 / 18,6 / 20,4 / 22,5 / 25,4 / 28,3 / 30,5 & 32,5 mm

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	5	72	
Width mm	33	45	150	300	
Depth mm	33	45	120	350	
Height mm	115	125	90	300	
Weight	130	175	938	14.4	
Packaging Information	Card use	0	Box	Case	
	Card gms	0	63	900	
	Plastic use	Tube	0	-	
	Plastic gms	45	0	0	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	