



RECHARGEABLE



## NEW AND IMPROVED STILL THE KING

**Rechargeable, waterproof (IP67)** and extremely versatile, the SLYDE KING 2K features a **2,000 lumen flashlight** with 4x zoom, and a **500 lumen C-O-B work light**. Each light mode is dimmable with programmable memory. The 2K also has an ergonomic **rubberized grip** and powerful **magnetic base**.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP
645397001027	NEB-WLT-1003	SLYDE KING 2K	32.29	59.99
645397001034	NEB-DSP-1004	SLYDE KING 2K Display	5.69	N/A

Display sold separately  
"Try Me" sample not included

Display Dimensions  
(H) 11.6" x (W) 7.5" x (D) 7.75"  
Gift Box Dimensions  
(H) 8.45" x (W) 1.75" x (D) 1.75"



# NEBO<sup>®</sup> SLYDE KING 2K

### FLASHLIGHT MODES

- High (2,000 lumens): 2 hours / 409 meters
- Low (200 lumens): 12 hours / 125 meters

### C-O-B WORK LIGHT MODES

- White High (500 lumens): 4 hours / 34 meters
- White Low (50 lumens): 24 hours / 10 meters
- Red High (40 lumens): 6 hours / 9 meters
- Red Low (4 lumens): 60 hours / 3 meters
- Red Flash (40 lumens): 6 hours / 9 meters

### DESIGN

- USB-C rechargeable
- OC™ Technology
- 4x adjustable zoom
- Dimming + Power Memory Setting
- Direct-to-Red
- Power indicator
- Battery charging indicator
- Rubberized grip
- Anodized aircraft-grade aluminum
- Waterproof (IP67) and impact-resistant
- Powerful magnetic base

### OPERATION

- Side-positioned backlit button with power indicator

### ACCESSORIES

- USB-C to USB charging cable
- Lanyard

### BATTERIES

- Powered by internal rechargeable battery  
(Recharge time: 4 - 8 hours, depending on output of USB)

### SPECS

- 1.0 lb.
- Length: 7.5" (Extended: 9.625")
- Diameter: 1.625" (head) / 1.375" (barrel)



CALIFORNIA REQUIRED ⚠️ WARNING | Cancer and Reproductive Harm | [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)