



Pushing Performance  
Since 1945

# Han B Hood Top Entry HC 4 Pegs PG 29



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 0421
Specification	Han B Hood Top Entry HC 4 Pegs PG 29
HARTING eCatalogue	<a href="https://b2b.harting.com/09300160421">https://b2b.harting.com/09300160421</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Type	High construction

## Version

Size	16 B
Version	Top entry
Number of cable entries	1
Cable entry	1x Pg 29
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12



**Pushing Performance**  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	190 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045811
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors