



Pushing Performance  
Since 1945

# Han Compact-HSE-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 008 0526
Specification	Han Compact-HSE-M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19120080526">https://b2b.harting.com/19120080526</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for standard cable gland With separate PE terminating point for all inserts of size Han-Compact®

## Version

Size	Han-Compact®
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/housings for industrial applications

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

## Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------



**Pushing Performance**  
Since 1945

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	300 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140124189
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors