



**Part Number :** [1300100917](#)  
**Product Description :** Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length  
**Series Number :** 130010  
**Status :** Active  
**Product Category :** Circular Industrial Cordsets  
**Engineering Number :** 114031K12M020



Documents & Resources

Drawings  
[1300100917\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Contains Lead per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                         |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474  
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                                                                                                                  |
|--------------|----------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                           |
| Category     | Circular Industrial Cordsets                                                                                                     |
| Series       | 130010                                                                                                                           |
| Description  | Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length |
| IP Rating    | IP67                                                                                                                             |
| Product Name | Mini-Change                                                                                                                      |
| Type         | Double Ended                                                                                                                     |
| UPC          | 78678884651                                                                                                                      |

#### Agency

|    |         |
|----|---------|
| UL | E152210 |
|----|---------|

#### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
| Voltage - Maximum             | 600V  |

#### Physical

|                         |                 |
|-------------------------|-----------------|
| Cable Diameter          | 10.67mm (.420") |
| Cable Length            | 2.0m (6.56')    |
| Color - Cable Jacket    | Yellow          |
| Connector End A         | Mini-Change     |
| Connector End B         | Mini-Change     |
| Coupling Style          | Threaded        |
| Gender                  | Female-Male     |
| Keyway                  | Single          |
| LED Indicator           | None            |
| Material - Cable Jacket | TPE             |

|                               |                         |
|-------------------------------|-------------------------|
| Material - Connector Body     | TPE                     |
| Material - Contact            | Copper Alloy            |
| Material - Coupling Nut       | Black Epoxy Coated Zinc |
| Material - Plating Mating     | Gold                    |
| Net Weight                    | 165.000/g               |
| Orientation                   | 90° to Straight         |
| Poles                         | 4                       |
| Temperature Range - Operating | -20° to +105°C          |
| Wire/Cable Type               | TC-ER                   |
| Wire Size (AWG)               | 16                      |