



Part Number : 1300130482

Product Description : Mini-Change A-Size
Receptacle, 5 Poles, 1/2" - 14 NPT Threads,
Female (90°) to 16 AWG Leads, 0.305m (1.0')
Length

Series Number : 130013

Status : Active

Product Category : Circular Industrial
Connectors

Engineering Number : 1R5005A20A120

Image coming soon

Documents & Resources

Drawings

1300130482_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change A-Size Receptacle, 5 Poles, 1/2" - 14 NPT Threads, Female (90°) to 16 AWG Leads, 0.305m (1.0') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678843941

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	0.305m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	1/2" - 14 NPT
Orientation	90° Angle
Panel Mount	N/A
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015

Wire Size (AWG)	16
-----------------	----