



Part Number : [1300940221](#)


Product Description : Standard Duty Support Grip, Double Eye, Closed Mesh, Double Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1428.82kg (3150 lbs)

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35007



Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Double Eye, Closed Mesh, Double Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1428.82kg (3150 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835007

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1428.82kg (3150 lbs)
Bale Length	0.152m (6.00")
Body Style	Straight
Cable Diameter	44.45-50.55mm (1.750-1.990")
Color - Grommet	N/A
Eye Type	Double
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.508m (20.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A