



**Part Number :** [1300940279](#)  
**Product Description :** Standard Duty Support Grip, Locking Bale, Closed Mesh, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 870.90kg (1920 lbs)  
**Series Number :** 130094  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 35095



---

## Documents & Resources

**Drawings**  
[PK-130227-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Locking Bale, Closed Mesh, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 870.90kg (1920 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835095

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	870.90kg (1920 lbs)
Bale Length	0.457m (18.00")
Body Style	Straight
Cable Diameter	38.10-44.20mm (1.500-1.740")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.432m (17.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A