



Part Number : [1300940391](#)
Product Description : Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 25.40-31.50mm (1.000-1.240"), Approximate Break Strength 762.04kg (1680 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 35288



Documents & Resources

Drawings
[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Cable Grips |
| Series | 130094 |
| Description | Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 25.40-31.50mm (1.000-1.240"), Approximate Break Strength 762.04kg (1680 lbs) |
| Product Name | Standard Duty |
| Type | Support Grip |
| UPC | 78678835288 |

Agency

| | |
|-----|---------|
| CSA | LR32159 |
|-----|---------|

Physical

| | |
|----------------------------|------------------------------|
| Approximate Break Strength | 762.04kg (1680 lbs) |
| Bale Length | 0.229m (9.00") |
| Body Style | Straight |
| Cable Diameter | 25.40-31.50mm (1.000-1.240") |
| Color - Grommet | N/A |
| Eye Type | Single |
| Gender | N/A |
| Material - Body | N/A |
| Material - Grip | Non-magnetic Tin Bronze Wire |
| Mesh Length | 0.38m (15.00") |
| Number of Holes | N/A |
| O-Ring | N/A |
| Thread Size | N/A |