



Part Number : [1300940399](#)
Product Description : Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1705.51kg (3760 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 35292



Documents & Resources

Drawings
[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1705.51kg (3760 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835292

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1705.51kg (3760 lbs)
Bale Length	0.406m (16.00")
Body Style	Straight
Cable Diameter	50.80-63.25mm (2.000-2.490")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.559m (22.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A