



Part Number : [1300940457](#)
Product Description : Heavy Duty Support Grip, Single Eye, Double Weave, Closed Mesh, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 1224.70kg (2700 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 35435



Documents & Resources

Drawings
[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Heavy Duty Support Grip, Single Eye, Double Weave, Closed Mesh, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 1224.70kg (2700 lbs)
Product Name	Heavy Duty
Type	Support Grip
UPC	78678835435

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1224.70kg (2700 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.66m (26.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A