



**Part Number :** 1300940470

**Product Description :** Heavy Duty Support Grip, Double Eye, Double Weave, Split Lace, Cable Diameter 38.10-50.55mm (1.500-1.990"), Approximate Break Strength 2140.96kg (4720 lbs)

**Series Number :** 130094

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 35443



---

## Documents & Resources

### Drawings

[PK-130227-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130094
Description	Heavy Duty Support Grip, Double Eye, Double Weave, Split Lace, Cable Diameter 38.10-50.55mm (1.500-1.990"), Approximate Break Strength 2140.96kg (4720 lbs)
Product Name	Heavy Duty
Type	Support Grip
UPC	78678835443

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	2140.96kg (4720 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	38.10-50.55mm (1.500-1.990")
Color - Grommet	N/A
Eye Type	Double
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.889m (35.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A