



Part Number : [1300980025](#)

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 1/4" NPT, Straight Male, Cable Diameter 3.43-5.08mm (.135-.200")

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Number : 5400



Documents & Resources

Drawings

[1300980025_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1/4" NPT, Straight Male, Cable Diameter 3.43-5.08mm (.135-.200")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678854000

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	3.43-5.08mm (.135-.200")
Color - Grommet	Gray
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	133.330/g
Number of Holes	1
O-Ring	No
Thread Size	1/4" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/4" NPT	<u>1300990141</u>
MAX-LOC Gasket Sealing Ring, 1/4" NPT, Black	<u>1300990147</u>

This document was generated on Feb 25, 2025