



Part Number : [1300980027](#)
Product Description : MAX-LOC Strain Relief
Cord-Sealing Grip, 3/8" NPT, Straight Male,
Cable Diameter 3.18-4.75mm (.125-.187")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5500




Documents & Resources

Drawings
[1300980027_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 3.18-4.75mm (.125-.187")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872110

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	3.18-4.75mm (.125-.187")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	32.498/g
Number of Holes	1
O-Ring	No
Thread Size	3/8" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/8" NPT	<u>1300990142</u>
MAX-LOC Gasket Sealing Ring, 3/8" NPT, Black	<u>1300990148</u>

This document was generated on Feb 25, 2025