



**Part Number :** 1300980090  
**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male with O-Ring, Cable Diameter 12.70-14.27mm (.500-.562")  
**Series Number :** 130098  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 5533W



## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Cable Grips

Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male with O-Ring, Cable Diameter 12.70-14.27mm (.500-.562")
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855332

## Agency

CSA	LR32159
UL	E76954

## Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	12.70-14.27mm (.500-.562")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	Yes
Thread Size	1/2" NPT

## Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>