



**Part Number :** [1300980112](#)  
**Product Description :** MAX-LOC Strain Relief  
Cord-Sealing Grip, 3/4" NPT, Straight Male,  
Cable Diameter 14.27-17.45mm (.562-.687")  
**Series Number :** 130098  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 5540



---

## Documents & Resources

**Drawings**  
[1300980112\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 14.27-17.45mm (.562-.687")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872125

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	14.27-17.45mm (.562-.687")
Color - Grommet	Green
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	1.000/g
Number of Holes	1
O-Ring	No
Thread Size	3/4" NPT

---

## Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

---

This document was generated on Feb 25, 2025