



Part Number : [1301070025](#)
Product Description : Super-Safeway
Assembled Rubber Stringlight Lampholder
with MAX-LOC Grips
Series Number : 130107
Status : Planned for Obsolescence
Product Category : Portable Lighting
Accessories
Engineering Number : 300W



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Planned for Obsolescence
Category	Portable Lighting Accessories
Series	130107
Description	Super-Safeway Assembled Rubber Stringlight Lampholder with MAX-LOC Grips
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	Accessory
UPC	78678861216

Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	N/A
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	46.48mm (1.830")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	99.06mm (3.900")
Lamp Type	A21
Length	180.34mm (7.100")
Material - Guard	N/A
Mounting Style	Stringer
Outlet	None
Packaging Type	Carton

This document was generated on Feb 25, 2025